


- 170.206.23
- 170.206.23 K1
- 170.206.23 KA
- 170.206.23 KM
- 170.206.23 KP
- 170.206.23 KR
- 170.206.23 M1
- 170.206.23 NU
- 170.206.23 PM
- 170.206.23 RG
- 170.206.23 RP
- 170.206.23 SM
- 170.206.23 SR



170.1902.18
LOXEAL 56-03
16 + 1 Nm

170.214.2
BECHEM
HIGH LUB SW2

170.104.17

4x170.1902.18
16 + 1 Nm

170.1003.12

29.1604.2

170.104.1

170.215.22

4x 23.1003.16

4x 170.1604.4

180.1506.26
BECHEM
HIGH LUB SW2

9.602.21
BECHEM
HIGH LUB SW2

170.6.8
BECHEM
HIGH LUB SW2

9.602.21
BECHEM
HIGH LUB SW2

170.602.111

4x 170.1603.22

170.1304.89
BECHEM
HIGH LUB SW2

4x 66.602.3

22.602.32
BECHEM
HIGH LUB SW2

170.208.169

170.1617.95

170.1904.6

26.1902.20
LOXEAL 56-03

170.201.6
LOXEAL 56-03

170.201.6
LOXEAL 56-03

170.201.7

170.201.7

170.201.7

170.201.7

170.201.7

170.201.7

170.201.7

170.201.7

170.201.7

170.201.7

170.201.7


170.201.7

170.201.7

170.201.7

170.201.7

170.201.7



SCALA SCALE 1:1
DIREZIONE ASSEMBLAGGIO 401.1006.7
LUBRIFICARE CON GRASSO MOLY LT2 1
COMPONENTI SOGGETTI A SFREGAMENTO
E ROTAZIONE
ASSEMBLY DIRECTION FOR 401.1006.7
LUBRICATE WITH MOLY LT2 GREASE THE
COMPONENTS SUBJECTED TO RUBBING AND
ROTATION

NON FORNITO CON VARIANTE K1 KA KM KP KR
NOT SUPPLIED WITH K1 KA KM KP KR MODELS

170.201.6
LOXEAL 56-03

SOLO VARIANTI K1 KA KM KP KR
K1 KA KM KP KR MODELS ONLY

68.602.10

167.1702.21

SOLO VARIANTI K1 KA KM KP KR
K1 KA KM KP KR MODELS ONLY

2x172.902.3

SOLO VARIANTI K1 KA KM KP KR
K1 KA KM KP KR MODELS ONLY

2x172.1607.5

SOLO VARIANTI K1 KA KM KP KR
K1 KA KM KP KR MODELS ONLY

180.602.30

NON FORNITO CON VARIANTE NU SM SR
NOT SUPPLIED WITH NU SM SR MODELS

170.1005.15

SOLO VARIANTE K1
ASSEMBLARE CON LOXEAL 56-03
SU 170.215.22
K1 MODEL ONLY
ASSEMBLE WITH LOXEAL 56-03
ON 170.215.22

SOLO VARIANTE M1
ASSEMBLARE SU 709.1504.59
M1 MODEL ONLY
ASSEMBLE ON 709.1504.59

SOLO VARIANTI KM KP PM RP
KM KP PM RP MODELS ONLY

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

180.1305.27

SOLO VARIANTI KP KR M1 RG RP SR
KP KR M1 RG RP SR MODELS ONLY

27.601.34

709.1304.79

709.605.87

709.1504.59
LOXEAL 56-03
SU 170.215.22

NON FORNITO CON VARIANTE K1 KA KM KP KR
NOT SUPPLIED WITH K1 KA KM KP KR MODELS

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

NON FORNITO CON VARIANTE NU
NOT SUPPLIED WITH NU MODEL

170.201.6
LOXEAL 56-03

170.201.6
LOXEAL 56-03

170.201.6
LOXEAL 56-03

170.201.6
LOXEAL 56-03

170.201.6
LOXEAL 56-03